

Motorpumps-Types	MP 06 P, MP 25P, MP60P
Discharge	From 100 to 5400 L/h
Standard operating pressure	up to 10 bars
Seal type	Mechanical sealing, packing-sealing
Viscosity	from 5 to 5000 cSt
Options	Gun, filter, dosage box
Tension	220-380 V triphased ou 220 V monophased
Drum	200L

