

LOW VISCOUS PRODUCT DRUM DRAINER

Cubic displacement per rotation	1
Speed rotation range in RPM	0 - 3200
Fluid viscosity range in cSt	1 - 20 000
Depression Bar	-0,6
Standard operating pressure in Bars	5
Operating temperature range in °C	-20 / +180
Pump body and stator material	Cast-Iron
Shaft and blades material	Steel
Built in By pass	Yes
Hard particles maximal size	200 microns
Soft particles maximal size	5 mm
Seal type	mecanical
Engine-Power Kw	0,37

