

Roof-mounted cooling units



Climate control accessories Page 369

Temperature control:

- Control of the server air infeed temperature

Material:

- Sheet steel

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- External circuit IP 34
- Internal circuit IP 54

Supply includes:

- Nano-coated condenser
- Integral electric condensate evaporation
- Fully wired ready for connection
- Drilling template
- Assembly parts

Note:

- A roof plate with cut-out to match the enclosure dimensions is required

for cooling IT equipment

Model No.	Packs of	3301.800	Page
Total cooling output L25 L35 W		3000	
Total cooling output L35 L45 W		3200	
Width mm		597	
Height mm		417	
Depth mm		895	
Rated operating voltage V, ~, Hz		230, 1~, 50	
Type of electrical connection		Plug-in terminal strip	
Pre-fuse (T) A		16	
Start-up current max. A		36	
Rated current max. A		9.2	
Refrigerant		R134a	
Permissible operating pressure (p. max.) bar		25	
Duty cycle %		100	
Operating temperature range		+10°C...+45°C	
Setting range		+20°C...+25°C	
Weight as delivered kg		72.0	
Accessories			
Condensate hose	1 pc(s).	3301.612	377
Door-operated switch	1 pc(s).	4127.010	639
Air baffle plates		see page	692
Filter mats	3 pc(s).	3286.500	369