

MANUAL DRUM DRAINER



Fluid viscosity range in cSt	5 - 40 000
Operating temperature range in °C	-20 à +70
Pump body and stator material	Cast Iron
Shaft and blades material	Steel
Hard particles maximal size	200 microns
Soft particles maximal size	5 mm
Seal type	Lip sealing

