

PNEUMATIC DRUM DRAINER



Cubic displacement per rotation	60
Speed rotation range in RPM	200
Discharge in L/min	12
Fluid viscosity range in cSt	5000 - 200 000
Standard operating pressure in Bars	5
Operating temperature range in °C	0/40
Pump body and stator material	Cast-Iron
Shaft and blades material	Steel
Built in By pass	No
Hard particles maximal size	200 microns
Soft particles maximal size	5 mm
Seal type	Tresses
Engine-Power Kw	2
Drum-Size	200L
Noise level	80dB
Option	Dosage

